## **Compressor Terminal Repair Kit**

Zebra Instruments offers a compressor terminal repair kit. The terminals are

high-temp soldered to the 10ga. Fine strand, color coded wires for the best connection. These special terminals allow clearance for compressor post, and lay flat under the safety cover, Twist on wire nuts also provided.



MARS NO.	DESCRIPTION	MARS PACK	CASE QTY.
08565	Compressor Terminal Repair Kit 1 set of 3, terminals/wires/connectors	1	24

## MARS Compressor Stake On Repair Kits



with the technician in mind!
During servicing of the air
conditioning system or
refrigeration system, it is not
unusual for a technician to
remove the compressor cover to
find the electrical connector or
spade terminal broken or melted
away from the compressor. In
reconnecting the electrical
power, the metal plate is often
found to have deteriorated to
such an extent that the
conventional female connector

will no longer attach to the spade



TERM-LOK

type male connector. Technology for reattaching a metal plate to the metal pin without damaging the encapsulated block is not normally available thus requiring the technician to attempt various types of crimping arrangements to avoid replacing the compressor assembly (which normally does not work).

The MARS Term-Lok is a brass cylindrical tube with a diameter large enough to slip over the pins and has a stainless set screw to lock onto the terminal. Term-Lok comes in packages of one or three terminal locks with color coded 65 strands, 600 volt permanently attached wire, with wrench provided for easy application. Once installed the compressor cover may be placed back over the terminals without any obstructions.

It takes approximately 15 minutes to install on most systems, thus saving the technician time and the customer money, with virtually no call backs.

MARS NO.	DESCRIPTION	MFG. NO.	CASE QTY.
86386	Brass stake on 12 gauge - 3 wire, 3' leads	TLC-3-12	1
86388	Brass stake on 10 gauge - 3 wire, 3' leads	TLC-3-10	1
86390	Brass stake on 8 gauge - 3 wire, 3' leads	TLC-3-8	1

## **Quick Disconnects - Insulated (105°C)**

MARS solderless terminals are competitively priced, yet manufactured of superior quality materials to rigid

quality control standards. Seams are brazed to ensure perfect crimps EVERY TIME!

MARS solderless terminals are UL listed and CSA certified.
Terminals are all manufactured in the USA. They are provided in clear, reclosable plastic display boxes. These attractive boxes, with clear and easy-to-read labels provide for visual inspection of the product and encourage impulse buying.

All packages display a MARS bar code for your convenience. MARS solderless terminals are available in two different package sizes. Both sizes enhance contractor self service. The MARS mini-pak display boxes contain very reasonable quantities with all types and sizes sold at one price. Perfect for the handyman, do-it-yourselfer and your sales and counter people. The MARS mini-



pak is excellent for that small, unique HVACR odd job. The MARS super-pak contains much larger quantities of the more common solderless terminals at a super value. The contractor and tradesman will make great use of this size reclosable package. Ask your MARS sales representative about our solderless terminal merchandiser program!

MARS NO.	MINI-PAK QTY.	SIZE	DESC	CRIPTION	MARS NO.	SUPER PAK QTY.
86200	20	22-18	.250 (1/4) fen	nale tab	86500	100
86201	20	16-14	.187 (3/16) fen	nale tab	86501	100
86202	20	16-14	.250 (1/4) fen	nale tab	86502	100
86203	15	12-10	.250 (1/4) fen	nale tab	86503	50
86219	20	22-18	.187 (3/16) fen	nale tab		
86205	20	16-14	.250 (1/4) ma	le tab	86505	100
86207	12	22-18	.250 (1/4) fen	nale full insul.	86507	100
86208	12	16-14	.250 (1/4) fen	nale full insul.	86508	100
86209	8	12-10	.250 (1/4) fen	nale full insul.	86509	50
86220	7	16-14	.250 (1/4) fen	nale flag fully insul.	86520	25
86221	6 pair		combo of #862	08, 09		
86211	12	16-14	.250 (1/4) ma	le fully insul.		
86216	12	22-18	.250 (1/4) ma	le/female p/back		
86217	12	16-14	.250 (1/4) ma	le/female p/back	86517	100
86218	8	12-10	.250 (1/4) ma	le/female p/back	86518	50